











Pulse Dampeners for 030 Pumps

Required Configurations			Additional Options (Not Required)			Rev
DBA030	I030	F	12	LF0	T	16
	①	②	③	④	⑤	⑥
						⑦

Bold = standard option

Please select one option from each of the required fields (1). To configure your dampener with different inlet and outlet fittings, leak detection, or request a specific revision level, please select options from the appropriate additional options (2-7). **DBA and DBH top mount dampeners are only compatible with A, H & R pumps and Legacy AP and X pumps. Please refer to spec sheet to confirm max temperature/pressure rating.**

Dampener	① ② ③ Size and Liquid Fitting Configuration		
	① Style	② Fitting Style (Inline only)	③ Fitting Size (Inline only)
DBA030	I030 Inline with 030 base	F = Flaretek® compatible 	04 = 1/4"
DBH030	T030 Top mount with 030 pump adapter	T = Tube Out 	06 = 3/8"
DBU030		W = Weldable 	08 = 1/2"
DBA060		P = Pillar S-300® <small>*Not available in 1/4" or 3/8"</small> 	12 = 3/4"
DBH060		N = Female NPT 	
DBU060		S = Synchro-Flare® <small>*Not available in 1/4"</small> 	







If the liquid inlet and outlet fitting styles are different, please define the liquid inlet fitting from section (2-3) and use the liquid outlet section below (5-6) to differentiate (inline only).

Optional Configurations

④ Leak Detection

LF0	= 15' fiber optic cable, no amplifier
LF1	= 15' fiber optic cable, with D10 amplifier
LF2	= 25' fiber optic cable, no amplifier
LF3	= 25' fiber optic cable, with D10 amplifier
LC0	= 15' conductivity cable
LC1	= 25' conductivity cable

⑤ ⑥ Liquid Outlet Fitting Configuration (if different from inlet, inline only)

⑤ Fitting Style (Inline Only)		⑥ Fitting Size	
F	= Flaretek® compatible 	04	= 1/4"
T	= Tube Out 	06	= 3/8"
W	= Weldable 	08	= 1/2"
P	= Pillar S-300® <small>*Not available in 1/4" or 3/8"</small> 	12	= 3/4"
N	= Female NPT 		
S	= Synchro-Flare® <small>*Not available in 1/4"</small> 		

If the liquid inlet and outlet fitting styles are different, please define the liquid outlet fitting from section 5-6 and use the liquid fitting section above (2-3) to differentiate (inline only).

⑦ Revision Level: Contact factory for copy exact code activation information.