

Configuration

FD12 - S - B F12

(optional)
F08 - 021

0. Model	1. Mount Position	2. Fitting Connection	3. Liquid Inlet	4. Liquid Outlet	5. Screen Orifice Diameter
----------	-------------------	-----------------------	-----------------	------------------	----------------------------

Instructions

A selection is required for each option.
 Contact support for revision or copy exact information.

Standard options are highlighted

0. Model	
1/2-in pre-filter (nominal for 030 products)	FD08
3/4-in pre-filter (nominal for 060 products)	FD12
1-in pre-filter (nominal for 140 products)	FD16

FD08 and FD12 are available product-mounted or standalone.
 FD16 are only available product-mounted.

1. Mount Position	
Product mounted	P
Standalone (in-line)	S

Standalone (in-line) pre-filters fit 030, 060, or 140 products.
 Product-mounted pre-filters fit their nominal equivalents.

5. Screen Orifice Diameter	
.043 Orifice	Blank
.021 Orifice	021



Blank options are not NPT nor any other standard. Pillar fittings require nut and ferrule and are NOT supplied by White Knight. Contact us for copy exact code activation information.

2. Fitting Connection	
Buttress connection	B
Machined into body	M

Liquid Fittings	3. Inlet	4. Outlet
No Fitting	X00	X00
Plugged	B00	B00
Machined 1/2 in. Flare	F08	F08
Machined 3/4 in. Flare	F12	F12
Flaretek Compatible	1/2 in.	F08
	3/4 in.	F12
	1 in.	F16
	1-1/4 in.	F20
Pillar S-300	3/8 in.	P06
	1/2 in.	P08
	3/4 in.	P12
	1 in.	P16
	1-1/4 in.	P20
PrimeLock	1/2 in.	L08
	3/4 in.	L12
	1 in.	L16
Machined 1 in. FNPT	N16	N16
FNPT	1/2 in.	N08
	3/4 in.	N12
	1 in.	N16
Tube Out	1/2 in.	T08
	3/4 in.	T12
	1 in.	T16
	1-1/4 in.	T20
Weldable	3/4 in.	W12
	1 in.	W16

Product Mounted Pre-Filters



Standalone (in-line) Pre-Filters



Model Compatibility			
Standalone (in-line)		Pump Mount	
Machined		Buttress	
FD08-S-M	FD12-S-M	FD12-S-B	FD16-P-B FD12-P-B FD08-P-B
		✓	✓
		✓	
✓			
	✓		
		✓	
		✓	
		✓	
		✓	
		✓	
		✓	
		✓	
	✓		
		✓	
		✓	
		✓	
		✓	
		✓	
		✓	
		✓	
		✓	

Fitting Connections

